




## ● FEATURE

- User Adjustable Parameter For Special Light Source
- Measure Most Popular Light Sources In Lux or Fc
- Removable Probe For Easy Access To The Source
- Cosine And Color Corrected Measurements
- Built-in Sensor With Protective Cover
- Min/Max Average And Auto Power Off
- Large LCD Display For Easy Reading
- Max/Min Function

**NEW!**

## ● SPECIFICATIONS

- **Measuring Range:**  
0.0 to 199.9/1999/19990/199900 lx  
Automatic/manual selection of range
- **Resolution:** 0.1 lx; 0.01 fc
- **Accuracy:**  
±3%rdg, 5dgts(standard A light source)
- **Angle deviation from cosine characteristics :**  
10° ± 1% 30° ± 2% 60° ± 5% 80° ± 20%
- **Temperature characteristics:**  
± 0.1% /°C (away from 25°C)
- **Response Time:** 0.5 sec
- **Light detector:** Si photo diode
- **Operation Temperature/ Humidity:**  
0°C to 40°C(32°F to 104°F); 0~80% RH
- **Storage Temperature/ Humidity:**  
-10°C to 60°C(14°F to 140°F); 0~70% RH
- **Over range:** “-OL-” display
- **Battery Type:** 1.5V type Size AA battery x 2
- **Battery Life:** 80 hours approx.
- **Dimensions:**  
169mm(L) x 63mm(W) x 37mm(H)  
6.7(L) x 2.5(W) x 1.5(H) inch
- **Weight:** approx. 210g
- **Accessories:** User's manual, Battery, Carrying case.
- **Preset Light Source Weighting:**  
L0: Standard Incandescent Light Source  
L1: LED White Daylight  
L2: LED Amber (Yellow) Light  
L3: LED Green Light  
L4: LED Red Light  
L5: LED Blue Light  
L6: Warm White Fluorescent Lamp  
L7: Cold White Fluorescent Lamp  
L8: User Setup Mode



*Detachable & Rotatable Light Sensor*

\* The specifications and other information in this catalogue are subject to change without prior notice.

**CENTER®**  
**CENTER TECHNOLOGY CORP.**

4F, No.415, Jung-Jeng Road, Shu-Lin Dist.,  
New Taipei City 238, Taiwan  
TEL: 886-2-26763926 E-Mail : center@centertek.com  
FAX: 886-2-26763925 http : //www.centertek.com



Distributed by:



Authorized Distributor  
APL ASIA CO., LTD.  
11/129-132 Moo.5 Lamlukka Rd., T.Kookut, A.Lamlukka, Pathumthani 12130 Thailand.  
TEL. 0-2995-4461-3, FAX. 0-2995-4464  
www.apl-asia.com  
EMAIL : sales@apl-asia.com  
LINE@ : @APL-ASIA